

Frequently Asked Questions

Q Can I use this fitting in my house water supply?

A Yes, the Hansen *Easy Fit* Compression Fittings are potable water approved.

Q Does this fitting carry Hansen's Limited Lifetime Warranty?

A Yes, all Hansen manufactured products carry our Limited Lifetime Warranty*

Q Can I use Hansen *Easy Fit* Fittings under driveways, paths and foundations?

A Hansen does not recommend the use of any Hansen *Easy Fit* Fittings under any driveways, paths, or foundations.

Q How tight should I tighten my *Easy Fit* Compression fittings?

A Up to 32mm just tighten hand tight and all sizes above use a spanner to tighten another 1/2 to 1 turns past hand tight. Remember you already have a seal once the pipe is past the O-Ring, all the Nut is doing is compressing the Grip Ring onto the pipe to hold the pipe in place.

Standards & Approvals



Approved for use with potable (drinkable) water. The Water Research Council in the UK is the highest recognised water testing organisation in the world.

AS/NZS 4020

Hansen *Easy Fit* Compression Fittings meet the requirements for products in contact with drinking water as per AS/NZS 4020 and AS/NZS 4129:2020 Australia & New Zealand drinking water standards.

AS/NZS 4129:2020



Hansen *Easy Fit* Compression Fittings have achieved the esteemed WaterMark Certification for use in plumbing & drainage installations. Certification No: WMKA21978


Hansen *Easy Fit* Compression Fittings are approved to be used in many municipal water supply construction and maintenance activities. See our website for details.




Easy to Install




1. Cut and chamfer the pipe with pipe cutters, knife or saw. Ensure a square cut of pipe ends. Clean burrs from pipe ends. Keep the pipe end clean and as free of scratches and imperfections as possible.



2. Undo the nut to the last thread, do not remove nut from the body.



3. Insert the pipe into the fitting through the Nut, White Grip Ring & Thrust Ring until it meets resistance at the Seal. Give the pipe a firm push past the Seal all the way until it hits the final stop point.



4. Firmly hand tighten the nut. Use a pair of poly grips for a further half turn past hand tight for final tightening on 40mm fittings and greater.

The hydraulic seal is created when the pipe passes the Seal. Tightening the nut is to achieve pull out resistance of the pipe.

Hansen *Easy Fit* Compression Fittings should be installed onto Medium Density pipe that has been installed in accordance with the following standards:

- AS/NZS 2566 Part 1 and Supplement "Buried Flexible Pipelines - Structural Design" Detailed Installation and Site Pressure Testing.
- AS/NZS 2566 Part 2 "Installation"
- AS/NZS 2033 Installation of Polyethylene Pipe Systems

For more information on best practice installations, please contact info@hansenproducts.com

Failure to complete installation in accordance with the above standards, may void any warranties given by Hansen Products (NZ) Limited in respect to the Fitting.

HANSEN PRODUCTS (NZ) LIMITED

PO Box 809 • Whangarei • New Zealand
P: +64 9 430 4140 F: +64 9 430 4141
E: info@hansenproducts.com
W: www.hansenproducts.com

Available From:

HANSEN

Best Installed Value



HDB205 2210

HANSEN[™]

Easy Fit Compression Fittings

www.hansenproducts.com

